

## AirQ 150

*The AirQ 150 appliance uses Prolitec's patented technology to diffuse fragrance and odor treatment products into the air. This appliance was designed to stand on a tabletop, desk, bookshelf, counter, or floor for directly diffusion into indoor commercial spaces.*

### Technical specifications

Type	Single nebulizer head
Cartridge	90mL recyclable
Droplet size	Typically less than one micron

### Power specifications

Input	100 – 240V AC at 0.6A
Frequency	50/60 Hz
Protection	Switched-mode power supply
Internal	3V backup battery
Output	15V DC at 1.0A

### Performance & Settings

Coverage	Up to 10,000 ft <sup>3</sup> (285m <sup>3</sup> )
Programs	Up to 3 start & stop times per day, 24/7 mode
Settings	50 intensity levels
Off-cycle	7 minutes
Enclosure	Polyethylene and polypropylene cover
Safety Approval	UL, CE, & FCC Part 15, ROHS compliant
Environment	0° to 40° C, <85% Humidity

### Dimensions & Installation

Size	5½" x 5½" x 6" (14.0cm x 14.0cm x 14.9cm)
Weight	3.1 lbs. (2.2kg) with full 90mL cartridge



1235 W. Canal Street  
Milwaukee, WI 53233, USA  
[www.airq.com](http://www.airq.com)  
Phone: +1 414 615 4630